

COMBO (Rigid/IMC or EMT) Bodies

By TayMac
Catalog # [CC0100](#)

1 in. Combo C Type Body



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

General

Application	For use with threaded Rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions.
Conduit Type	Combination
Fitting Type	Conduit Bodies
Material	Aluminum
Type	C Type Conduit Bodies
UPC	050169815083

Dimensions

Dimensions	6.457 in x 1.819 in x 1.89 in
Height	1.89 in
Length	6.457 in
Trade Size	1 in
Weight	0.395 lb
Width	1.819 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	25
Minimum Pack Quantity	5
Pallet Quantity	1250

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-CC0100-SPEC-EN | REV 6/2024