

COMBO (Rigid/IMC or EMT) Bodies

By TayMac
Catalog # [CLB050](#)



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

Application

For use with threaded Rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions.

General

Catalog Number	CLB050
Conduit Type	Combination
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LB Type Conduit Bodies
UPC	050169815182

Dimensions

Dimensions	4.311 in x 1.339 in x 2.087 in
Height	2.087 in
Length	4.311 in
Trade Size	1/2 in

Weight	0.208 lb
Width	1.339 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	100
Minimum Pack Quantity	10
Pallet Quantity	1800

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Certifications - UL COC-E212332-1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - CLB050](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac:® Aluminum Series Conduit Bodies](#)