

COMBO (Rigid/IMC or EMT) Bodies

By TayMac
Catalog # [CLB150](#)



1-1/2 in. Combo LB Type Body

*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

Application

For use with threaded Rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions.

General

Catalog Number	CLB150
Conduit Type	Combination
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LB Type Conduit Bodies
UPC	050169815229

Dimensions

Dimensions	7.819 in x 2.508 in x 3.524 in
Height	3.524 in
Length	7.819 in
Trade Size	1-1/2 in

Weight	0.925 lb
Width	2.508 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Minimum Pack Quantity	2
Pallet Quantity	480

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Specifications - CLB150](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac:® Aluminum Series Conduit Bodies](#)