

COMBO (Rigid/IMC or EMT) Bodies

By TayMac
Catalog # [CLL050](#)

1/2 in. Combo LL Type Body



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

General

Application	For use with threaded Rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions
Conduit Type	Combination
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LL Type Conduit Bodies
UPC	050169815304

Dimensions

Dimensions	4.311 in x 2.028 in x 1.358 in
Height	1.358 in
Length	4.311 in
Trade Size	1/2 in
Weight	0.238 lb
Width	2.028 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	100
Minimum Pack Quantity	10
Pallet Quantity	2400

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-CLL050-SPEC-EN | REV 6/2024