



COMBO (Rigid/IMC or EMT) Bodies

By TayMac
Catalog # [CLR100](#)

1 in. Combo LR Type Body



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

General

| | |
|--------------|---|
| Application | For use with threaded Rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions. |
| Conduit Type | Combination |
| Fitting Type | Conduit Bodies |
| Material | Aluminum |
| Type | LR Type Conduit Bodies |
| UPC | 050169815441 |

Dimensions

| | |
|------------|-------------------------------|
| Dimensions | 5.919 in x 2.681 in x 1.89 in |
| Height | 1.89 in |
| Length | 5.919 in |
| Trade Size | 1 in |
| Weight | 0.424 lb |
| Width | 2.681 in |

Certifications And Compliance

| | |
|-------------|-----------|
| NEC | Compliant |
| Nema Rating | NEMA 3R |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 5 |
| Pallet Quantity | 1000 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-CLR100-SPEC-EN | REV 6/2024