



COMBO (Rigid/IMC or EMT) Bodies

By TayMac

Catalog # [COC125](#)

1-1/4 in. Combo C Assembly



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

General

Application	For use with threaded Rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.
Conduit Type	Combination
Fitting Type	Conduit Bodies
Material	Aluminum
Type	C Type Conduit Bodies
UPC	050169815038

Dimensions

Dimensions	8.346 in x 2.508 in x 2.736 in
Height	2.736 in
Length	8.346 in
Trade Size	1-1/4 in
Weight	1.013 lb
Width	2.508 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Minimum Pack Quantity	2
Pallet Quantity	640

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Certifications - UL COC-E212332-1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-COC125-SPEC-EN | REV 6/2024