



COMBO (Rigid/IMC or EMT) Bodies

By TayMac
Catalog # COLB150

1-1/2 in. Combo LB Assembly



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

Application

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

General

Conduit Type	Combination
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LB Type Conduit Bodies
UPC	050169815168

Dimensions

Dimensions	7.819 in x 2.508 in x 3.76 in
Height	3.76 in
Length	7.819 in
Trade Size	1-1/2 in
Weight	1.099 lb
Width	2.508 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Minimum Pack Quantity	2
Pallet Quantity	480

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
TAYM-COLB150-SPEC-EN | REV 6/2024