



## COMBO (Rigid/IMC or EMT) Bodies

By TayMac  
Catalog # [COLL075](#)

3/4 in. Combo LL Assembly



\*Representative Image

### Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

### Application

For use with threaded Rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

### General

Conduit Type	Combination
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LL Type Conduit Bodies
UPC	050169815250

### Dimensions

Dimensions	5.083 in x 2.303 in x 1.862 in
Height	1.862 in
Length	5.083 in
Trade Size	3/4 in
Weight	0.365 lb
Width	2.303 in

### Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	50
Minimum Pack Quantity	10
Pallet Quantity	1600

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Certifications - UL COC-E212332-1](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
TAYM-COLL075-SPEC-EN | REV 6/2024