



COMBO (Rigid/IMC or EMT) Bodies

By TayMac
Catalog # COLR150

1-1/2 in. Combo LR Assembly



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

General

Application	For use with threaded Rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.
Conduit Type	Combination
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LR Type Conduit Bodies
UPC	050169815403

Dimensions

Dimensions	7.819 in x 3.52 in x 2.736 in
Height	2.736 in
Length	7.819 in
Trade Size	1-1/2 in
Weight	1.078 lb
Width	3.52 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Minimum Pack Quantity	2
Pallet Quantity	480

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Certifications - UL COC-E212332-1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-COLR150-SPEC-EN | REV 6/2024