

COMBO (Rigid/IMC or EMT) Bodies

By TayMac
Catalog # [COT200](#)



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

Application

For use with threaded Rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

General

Catalog Number	COT200
Conduit Type	Combination
Fitting Type	Conduit Bodies
Material	Aluminum
Type	T Type Conduit Bodies
UPC	050169815533

Dimensions

Dimensions	10.551 in x 4.272 in x 3.642 in
Height	3.642 in

Length	10.551 in
Trade Size	2 in
Weight	1.764 lb
Width	4.272 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	280

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Certifications - UL COC-E212332-1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - COT200](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac:® Aluminum Series Conduit Bodies](#)