



## CONDUIT BODY GASKETS

By TayMac  
Catalog # [CRG125](#)

1-1/4 in. Conduit Body Rubber Gasket



\*Representative Image

### Features

Color - Black.

### General

EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Rubber
Type	Conduit Body Replacement Parts
UPC	092326213745

### Dimensions

Dimensions	2.188 in x 4 in x 4 in
Height	4 in
Length	2.188 in
Trade Size	1-1/4 in
Weight	0.059 lb
Width	4 in

### Certifications And Compliance

Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	200
Minimum Pack Quantity	200
Pallet Quantity	30000

### Product Assets

[Brochures - TayMac® Conduit Bodies](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
TAYM-CRG125-SPEC-EN | REV 6/2024