



EMT Conduit Bodies

By TayMac
Catalog # [EAT250](#)

2-1/2 in. EMT T Assembly



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

Application

For use with EMT conduit, for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

General

Catalog Number	EAT250
Conduit Type	EMT
Fitting Type	Conduit Bodies
Material	Aluminum
Type	T Type Conduit Bodies
UPC	050169816462

Dimensions

Dimensions	13.465 in x 5.886 in x 4.291 in
Height	4.291 in

Length	13.465 in
Trade Size	2-1/2 in
Weight	3.704 lb
Width	5.886 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	1
Pallet Quantity	120

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Certifications - UL COC-E212332-1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - EAT250](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac:® Aluminum Series Conduit Bodies](#)