

## Rigid/IMC Conduit Bodies

By TayMac  
Catalog # [LB150](#)

1-1/2 in. Rigid LB Assembly



\*Representative Image

### Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

### General

Application	For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions
Conduit Type	Rigid/IMC
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LB Type Conduit Bodies
UPC	050169816745

### Dimensions

Dimensions	7.819 in x 2.508 in x 3.524 in
Height	3.524 in
Length	7.819 in
Trade Size	1-1/2 in
Weight	0.907 lb
Width	2.508 in

### Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	10
Minimum Pack Quantity	2
Pallet Quantity	480

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Sales Drawings - LB\\_ConduitBody](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
TAYM-LB150-SPEC-EN | REV 6/2024