



## Rigid/IMC Conduit Bodies

By TayMac  
Catalog # [LL200](#)

2 in. Rigid LL Type Body



\*Representative Image

### Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

### Application

For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions

### General

Conduit Type	Rigid/IMC
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LL Type Conduit Bodies
UPC	050169816851

### Dimensions

Dimensions	10.051 in x 4.272 in x 3.406 in
Height	3.406 in
Length	10.051 in
Trade Size	2 in
Weight	1.497 lb
Width	4.272 in

### Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	5
Pallet Quantity	180

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Certifications - UL COC-E212332-1](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
TAYM-LL200-SPEC-EN | REV 6/2024