

## Rigid/IMC Conduit Bodies

By TayMac  
 Catalog # [LL250](#)

2-1/2 in. Rigid LL Type Body



\*Representative Image

### Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

### General

Application	For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions
Conduit Type	Rigid/IMC
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LL Type Conduit Bodies
UPC	050169816868

### Dimensions

Dimensions	12.835 in x 5.886 in x 3.976 in
Height	3.976 in
Length	12.835 in
Trade Size	2-1/2 in
Weight	2.879 lb
Width	5.886 in

### Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	1
Pallet Quantity	120

### Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)
- [Certifications - UL COC-E212332-1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
TAYM-LL250-SPEC-EN | REV 6/2024