



Rigid/IMC Conduit Bodies

By TayMac
Catalog # [LL400](#)

4 in. Rigid LL Type Body



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

General

Application	For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions
Conduit Type	Rigid/IMC
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LL Type Conduit Bodies
UPC	050169816899

Dimensions

Dimensions	15.65 in x 7.657 in x 5.591 in
Height	5.591 in
Length	15.65 in
Trade Size	4 in
Weight	6.113 lb
Width	7.657 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	1
Pallet Quantity	60

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-LL400-SPEC-EN | REV 6/2024