



## Rigid/IMC Conduit Bodies

By TayMac  
Catalog # [LR0100](#)

1 in. Rigid LR Type Body



\*Representative Image

### Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

### General

Application	For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions
Conduit Type	Rigid/IMC
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LR Type Conduit Bodies
UPC	050169816929

### Dimensions

Dimensions	5.919 in x 2.681 in x 1.89 in
Height	1.89 in
Length	5.919 in
Trade Size	1 in
Weight	0.415 lb
Width	2.681 in

### Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	25
Minimum Pack Quantity	5
Pallet Quantity	1000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
TAYM-LR0100-SPEC-EN | REV 6/2024