



Rigid/IMC Conduit Bodies

By TayMac
Catalog # [LR125](#)

1-1/4 in. Rigid LR Type Body



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

Application

For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions

General

Conduit Type	Rigid/IMC
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LR Type Conduit Bodies
UPC	050169816936

Dimensions

Dimensions	7.819 in x 3.52 in x 2.5 in
Height	2.5 in
Length	7.819 in
Trade Size	1-1/4 in
Weight	0.922 lb
Width	3.52 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Minimum Pack Quantity	2
Pallet Quantity	480

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
TAYM-LR125-SPEC-EN | REV 6/2024