



1-Gang Weatherproof Flip Cover, Horizontal/Vertical, Flat, 16-in-1, Gray

By TayMac
Catalog # [MM110G](#)

1-Gang Weatherproof Flip Cover, Horizontal/Vertical, Flat, 16-in-1, Gray



Features

- High-impact polycarbonate construction provides maximum durability
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast) for 16-in-1 custom device configurations, comes pre-configured for GFCI
- Lockable tab (1/8 in. shackle)
- Includes attached gasket and mounting hardware
- Horizontal or vertical device mount

General

Application	Flat
Catalog Number	MM110G
Color	Gray
Construction	Nonmetallic
Cover Type	Blank/Flat
EU RoHS Indicator	Contact Manufacturer
Material	Polycarbonate
Mounting Method	Multi-directional
Number of Gang(s)	1-Gang
Type	Cover
UPC	092326100601

Dimensions

Actual Depth	1.55 in
Cubic Capacity	13.3588125 cu.in
Depth	0.625 in
Height	3.81 in
Weight	0.328 lb
Width	5.61 in

Certifications And Compliance

Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Packaging Type	Shrink
Pallet Quantity	1890
Standard Package	10

Product Assets

[Brochures - Non-metallic Weatherproof Boxes, Covers & Lighting](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Sales Drawings - MM110](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-MM110G-SPEC-EN | REV 6/2024