



## 2-Gang Weatherproof Flip Cover, 55-in-1, Flat, Gray

By TayMac  
Catalog # [MM1410G](#)

2-Gang Weatherproof Flip Cover, 55-in-1, Flat, Gray



### Features

- High-impact polycarbonate construction provides maximum durability
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast) for 55-in-1 custom device configurations, comes pre-configured for GFCI
- Includes attached gasket and mounting hardware
- Lockable tab

### General

Application	Flat
Catalog Number	MM1410G
Color	Gray
Construction	Nonmetallic
Cover Type	Blank/Flat
EU RoHS Indicator	Contact Manufacturer
Material	Polycarbonate
Mounting Method	Vertical
Number of Gang(s)	2-Gang
Type	Cover
UPC	092326100632

### Dimensions

Actual Depth	3.1 in
Cubic Capacity	14.127 cu.in
Depth	0.625 in
Height	5.54 in
Weight	0.559 lb
Width	4.08 in

### Certifications And Compliance

Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	10
Packaging Type	Shrink
Pallet Quantity	960
Standard Package	10

### Product Assets

[Brochures - Non-metallic Weatherproof Boxes, Covers & Lighting](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)  
[Certifications - UL COC-E116141-4](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Sales Drawings - MM1410](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
TAYM-MM1410G-SPEC-EN | REV 6/2024