



## 2-Gang Weatherproof In-Use Cover, 55-in-1, 2-3/4 in. Deep, Gray

By TayMac  
Catalog # [MM2410G](#)

2-Gang Weatherproof In-Use Cover, 55-in-1, 2-3/4 in. Deep, Gray



### Features

- High-impact polycarbonate construction provides maximum durability
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast) for 55-in-1 custom device configurations, comes pre-configured for GFCI
- Includes attached gasket and mounting hardware
- Lockable tab

### General

Application	In Use
Catalog Number	MM2410G
Color	Gray
Construction	Nonmetallic
Cover Type	In-Use
EU RoHS Indicator	Contact Manufacturer
Material	Polycarbonate
Mounting Method	Vertical
Number of Gang(s)	2-Gang
Type	Cover
UPC	092326104050

### Dimensions

Actual Depth	3.25 in
Cubic Capacity	86.96875 cu.in
Depth	2.75 in
Height	5.75 in
Weight	0.7 lb
Width	5.5 in

### Certifications And Compliance

Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	6
Packaging Type	Shrink
Pallet Quantity	576
Standard Package	6

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)  
[Certifications - UL COC-E116141-4](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Sales Drawings - MM2410](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
TAYM-MM2410G-SPEC-EN | REV 6/2024