



2-Gang Weatherproof In-Use Cover, EXTRA DUTY®, 55-in-1, 2-3/4 in. Deep, Gray

By TayMac
Catalog # [MM2420G](#)

2-Gang Weatherproof In-Use Cover, EXTRA DUTY®, 55-in-1, 2-3/4 in. Deep, Gray



Features

- High-impact polycarbonate construction provides maximum durability
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast)for 55-in-1 custom device configurations, comes pre-configured for GFCI
- Lockable tab (1/8 in. shackle)
- Extra Duty® rated
- Includes attached gasket and mounting hardware
- 2.75 in. deep
- Vertical mount

General

Application	In Use
Catalog Number	MM2420G
Color	Gray
Construction	Nonmetallic
Cover Type	In-Use
Material	Polycarbonate
Mounting Method	Vertical
Number of Gang(s)	2-Gang
Type	Cover
	Cover
UPC	050169916629

Dimensions

Actual Depth	3.07 in
Cubic Capacity	82.72605 cu.in
Depth	2.75 in
Height	5.54 in
Weight	0.775 lb
Width	5.43 in

Certifications And Compliance

Certified Listed Compliance	UL Listed Extra-Duty Compliant
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	4
Packaging Type	Shrink
Pallet Quantity	384
Standard Package	6

Product Assets

- [Brochures - TayMac Extra Duty In-use Covers](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Product Logo - ExtraDuty](#)
- [Sales Drawings - MM2420](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TAYMAC: Extra-Duty Overview](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-MM2420G-SPEC-EN | REV 6/2024