



# 1-Gang Weatherproof In-Use Cover, EXTRA DUTY®, 16-in-1, 2-3/4 in. Deep, Gray

By TayMac  
Catalog # [MM420G](#)

1-Gang Weatherproof In-Use Cover, EXTRA DUTY®, 16-in-1, 2-3/4 in. Deep, Gray



## Features

- High-impact polycarbonate construction provides maximum durability
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast) for 16-in-1 custom device configurations, comes pre-configured for GFCI
- Includes attached gasket and mounting hardware
- Lockable tab (1/4 in. shackle)
- Extra Duty® rated
- Horizontal or vertical mount

## General

Color	Gray
Construction	Nonmetallic
Cover Type	In-Use
Material	Polycarbonate
Mounting Method	Multi-directional
Number of Gang(s)	1-Gang
Type	Cover
UPC	050169917282

## Dimensions

Actual Depth	2.995 in
Cubic Capacity	73.5229935 cu.in
Depth	2.75 in
Height	5.898 in
Weight	0.457 lb
Width	4.533 in

## Certifications And Compliance

Certified Listed	cULus Listed
NEC	Compliant
Nema Rating	NEMA 3R

## Logistics

Carton Quantity	8
Packaging Type	Shrink
Pallet Quantity	768
Standard Package	8

## Product Assets

[Brochures - TayMac Extra Duty In-use Covers](#)  
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Certifications - UL COC-E116141-4](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Product Logo - ExtraDuty](#)  
[Sales Drawings - MM420](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - TAYMAC: Weatherproof Extra Duty In-use Covers](#)  
[Video - TAYMAC: Extra-Duty Overview](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
TAYM-MM420G-SPEC-EN | REV 6/2024