



## Rigid/IMC Conduit Bodies

By TayMac  
Catalog # [RC075](#)

3/4 in. Rigid C Type Body



\*Representative Image

### Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

### Application

For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions

### General

Conduit Type	Rigid/IMC
Fitting Type	Conduit Bodies
Material	Aluminum
Type	C Type Conduit Bodies
UPC	050169816615

### Dimensions

Dimensions	5.512 in x 1.563 in x 1.626 in
Height	1.626 in
Length	5.512 in
Trade Size	3/4 in
Weight	0.266 lb
Width	1.563 in

### Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	50
Minimum Pack Quantity	10
Pallet Quantity	2000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Certifications - UL COC-E212332-1](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
TAYM-RC075-SPEC-EN | REV 6/2024