

## Rigid/IMC Conduit Bodies

By TayMac  
Catalog # [RC250](#)

2-1/2 in. Rigid C Type Body



\*Representative Image

### Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

### General

Application	For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions
Conduit Type	Rigid/IMC
Fitting Type	Conduit Bodies
Material	Aluminum
Type	C Type Conduit Bodies
UPC	050169816660

### Dimensions

Dimensions	13.465 in x 4.488 in x 3.976 in
Height	3.976 in
Length	13.465 in
Trade Size	2-1/2 in
Weight	2.754 lb
Width	4.488 in

### Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	1
Pallet Quantity	168

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Certifications - UL COC-E212332-1](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
TAYM-RC250-SPEC-EN | REV 6/2024