

RIGID/IMC CONDUIT BODIES

By TayMac
 Catalog # [RLB350](#)

3-1/2 in. Rigid LB Assembly



*Representative Image

Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

General

Catalog Number	RLB350
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LB Type Conduit Bodies
UPC	092326213127

Dimensions

Cubic Capacity	323 cu.in
Dimensions	15.65 in x 5.55 in x 7.09 in
Height	7.09 in
Length	15.65 in
Trade Size	3-1/2 in
Weight	7.7 lb

Width	5.55 in
-------	---------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	1
Pallet Quantity	50
Standard Package	1

Product Assets

- Brochures - [TayMac® Conduit Bodies](#)
- Catalogs - [RACO / TayMac / Bell Full Catalog](#)
- Catalogs - [In-Use Covers and Conduit Bodies C1-C40_1](#)
- Certifications - [UL COC-E212332-1](#)
- Customer Notices - [Prop 65 - Cancer & Reproductive Harm Notice](#)
- SDS - [HCC SDS](#)
- Specifications - [RLB350](#)
- Terms and Conditions - [HCC Terms & Conditions](#)
- Video - [TayMac:® Aluminum Series Conduit Bodies](#)