

RIGID/IMC CONDUIT BODIES

By TayMac
Catalog # RLB400

4 in. Rigid LB Assembly



*Representative Image

Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

General

Catalog Number	RLB400
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	LB Type Conduit Bodies
UPC	092326213134

Dimensions

Cubic Capacity	323 cu.in
Dimensions	15.65 in x 5.55 in x 7.09 in
Height	7.09 in
Length	15.65 in
Trade Size	4 in

Weight	7.7 lb
Width	5.55 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	1
Standard Package	1

Product Assets

[Brochures - TayMac® Conduit Bodies](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)