



RIGID/IMC CONDUIT BODIES

By TayMac
Catalog # [RLC050](#)

1/2 in. Rigid C Assembly



*Representative Image

Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	C Type Conduit Bodies
UPC	092326211970

Dimensions

Cubic Capacity	4.3 cu.in
Dimensions	4.72 in x 1.34 in x 1.36 in
Height	1.36 in
Length	4.72 in
Trade Size	1/2 in
Weight	0.29 lb
Width	1.34 in

Certifications And Compliance

Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	5
Pallet Quantity	3240
Standard Package	5

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
TAYM-RLC050-SPEC-EN | REV 6/2024