

RIGID/IMC CONDUIT BODIES

By TayMac
Catalog # [RLC075](#)

3/4 in. Rigid C Assembly



*Representative Image

Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

General

Catalog Number	RLC075
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	C Type Conduit Bodies
UPC	092326211987

Dimensions

Cubic Capacity	7.3 cu.in
Dimensions	5.51 in x 1.56 in x 1.63 in
Height	1.63 in
Length	5.51 in
Trade Size	3/4 in
Weight	0.4 lb

Width	1.56 in
-------	---------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	5
Pallet Quantity	2400
Standard Package	5

Product Assets

[Brochures - TayMac® Conduit Bodies](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Specifications - RLC075](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac:® Aluminum Series Conduit Bodies](#)