

## RIGID/IMC CONDUIT BODIES

By TayMac  
Catalog # RLC150

1-1/2 in. Rigid C Assembly



\*Representative Image

### Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

### General

Catalog Number	RLC150
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	C Type Conduit Bodies
UPC	092326213165

### Dimensions

Cubic Capacity	34.2 cu.in
Dimensions	8.35 in x 2.51 in x 2.5 in
Height	2.5 in
Length	8.35 in
Trade Size	1-1/2 in

Weight	1.1 lb
Width	2.51 in

### Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	2
Standard Package	2

### Product Assets

[Brochures - TayMac® Conduit Bodies](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)  
[Certifications - UL COC-E212332-1](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - TayMac: Aluminum Series Conduit Bodies](#)