

RIGID/IMC CONDUIT BODIES

By TayMac
 Catalog # [RLT250](#)

2-1/2 in. Rigid T Assembly



*Representative Image

Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

General

Catalog Number	RLT250
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	T Type Conduit Bodies
UPC	092326213462

Dimensions

Cubic Capacity	157.4 cu.in
Dimensions	13.46 in x 5.89 in x 3.98 in
Height	3.98 in
Length	13.46 in
Trade Size	2-1/2 in
Weight	4.1 lb

Width	5.89 in
-------	---------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	1
Pallet Quantity	105
Standard Package	1

Product Assets

- [Brochures - TayMac® Conduit Bodies](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Certifications - UL COC-E212332-1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - RLT250](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac:® Aluminum Series Conduit Bodies](#)