

RIGID/IMC CONDUIT BODIES

By TayMac
Catalog # [RLT400](#)

4 in. Rigid T Assembly



*Representative Image

Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	T Type Conduit Bodies
UPC	092326213493

Dimensions

Cubic Capacity	323 cu.in
Dimensions	16.3 in x 7.66 in x 5.59 in
Height	5.59 in
Length	16.3 in
Trade Size	4 in
Weight	7.9 lb
Width	7.66 in

Certifications And Compliance

Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	1
Pallet Quantity	50
Standard Package	1

Product Assets

[Brochures - TayMac® Conduit Bodies](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-RLT400-SPEC-EN | REV 6/2024