



RIGID/IMC CONDUIT BODIES

By TayMac
Catalog # RSLB050

1/2 in. Rigid SLB



*Representative Image

Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	Service Entrance SLB Conduit Bodies
UPC	092326212458

Dimensions

Dimensions	1.58 in x 3.25 in x 1.39 in
Height	1.39 in
Length	1.58 in
Trade Size	1/2 in
Weight	0.19 lb
Width	3.25 in

Certifications And Compliance

Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Pallet Quantity	5280
Standard Package	10

Product Assets

- [Brochures - TayMac® Conduit Bodies](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-RSLB050-SPEC-EN | REV 6/2024