



## RIGID/IMC CONDUIT BODIES

By TayMac  
Catalog # RSLB075

3/4 in. Rigid SLB



\*Representative Image

### Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

### General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	Service Entrance SLB Conduit Bodies
UPC	092326212465

### Dimensions

Dimensions	1.88 in x 3.64 in x 1.7 in
Height	1.7 in
Length	1.88 in
Trade Size	3/4 in
Weight	0.3 lb
Width	3.64 in

### Certifications And Compliance

Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	5
Pallet Quantity	3600
Standard Package	5

### Product Assets

- [Brochures - TayMac® Conduit Bodies](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40\\_1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
TAYM-RSLB075-SPEC-EN | REV 6/2024