



RIGID/IMC CONDUIT BODIES

By TayMac
Catalog # RSLB100

1 in. Rigid SLB



*Representative Image

Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	Service Entrance SLB Conduit Bodies
UPC	092326212472

Dimensions

Dimensions	2.1 in x 4.23 in x 1.92 in
Height	1.92 in
Length	2.1 in
Trade Size	1 in
Weight	0.433 lb
Width	4.23 in

Certifications And Compliance

Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	3
Pallet Quantity	1890
Standard Package	3

Product Assets

- [Brochures - TayMac® Conduit Bodies](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-RSLB100-SPEC-EN | REV 6/2024