



RIGID/IMC CONDUIT BODIES

By TayMac
Catalog # RSLB125

1-1/4 in. Rigid SLB



*Representative Image

Features

- Durable die cast aluminum construction.
- Premium powder coat finish.
- Includes NBR synthetic rubber gasket.
- Stamped aluminum cover.
- Combination head screw.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Conduit Bodies
Material	Aluminum
Type	Service Entrance SLB Conduit Bodies
UPC	092326212489

Dimensions

Dimensions	2.58 in x 5.5 in x 2.38 in
Height	2.38 in
Length	2.58 in
Trade Size	1-1/4 in
Weight	0.7 lb
Width	5.5 in

Certifications And Compliance

Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	2
Pallet Quantity	780
Standard Package	2

Product Assets

- [Brochures - TayMac® Conduit Bodies](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-RSLB125-SPEC-EN | REV 6/2024