

Rigid/IMC Conduit Bodies

By TayMac
 Catalog # [T075](#)

3/4 in. Rigid T Type Body



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

Application

For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions

General

Catalog Number	T075
Conduit Type	Rigid/IMC
Fitting Type	Conduit Bodies
Material	Aluminum
Type	T Type Conduit Bodies
UPC	050169817018

Dimensions

Dimensions	5.512 in x 2.303 in x 1.626 in
Height	1.626 in
Length	5.512 in
Trade Size	3/4 in

Weight	0.303 lb
Width	2.303 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	50
Pallet Quantity	1500
Standard Package	10

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
- [Certifications - UL COC-E212332-1](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - T075](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - TayMac:® Aluminum Series Conduit Bodies](#)