

Rigid/IMC Conduit Bodies

By TayMac
Catalog # T250

2-1/2 in. Rigid T Type Body



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

General

| | |
|--------------|-------------------------------------------------------------------------------------------------------|
| Application | For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions |
| Conduit Type | Rigid/IMC |
| Fitting Type | Conduit Bodies |
| Material | Aluminum |
| Type | T Type Conduit Bodies |
| UPC | 050169817063 |

Dimensions

| | |
|------------|---------------------------------|
| Dimensions | 13.465 in x 5.886 in x 3.976 in |
| Height | 3.976 in |
| Length | 13.465 in |
| Trade Size | 2-1/2 in |
| Weight | 3.003 lb |
| Width | 5.886 in |

Certifications And Compliance

| | |
|-------------|-----------|
| NEC | Compliant |
| Nema Rating | NEMA 3R |

Logistics

| | |
|------------------|-----|
| Carton Quantity | 1 |
| Pallet Quantity | 120 |
| Standard Package | 1 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-T250-SPEC-EN | REV 6/2024