

Rigid/IMC Conduit Bodies

By TayMac
Catalog # T350

3-1/2 in. Rigid T Type Body



*Representative Image

Features

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

General

Application	For use with threaded Rigid/IMC conduit, for pullig access or to split a run into multiple directions
Conduit Type	Rigid/IMC
Fitting Type	Conduit Bodies
Material	Aluminum
Type	T Type Conduit Bodies
UPC	050169817087

Dimensions

Dimensions	16.299 in x 7.657 in x 5.591 in
Height	5.591 in
Length	16.299 in
Trade Size	3-1/2 in
Weight	7.004 lb
Width	7.657 in

Certifications And Compliance

NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	1
Pallet Quantity	60
Standard Package	1

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Certifications - UL COC-E212332-1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TayMac: Aluminum Series Conduit Bodies](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
TAYM-T350-SPEC-EN | REV 6/2024