



UNIVERSAL CONDUIT BODIES

By TayMac
Catalog # [UCB075](#)

3/4 in. Universal Conduit Body



Features

- Seamless pre-affixed gasket and self-aligning covers/panels
- More wiring capacity than standard bodies and meets 2014 NEC 314.16(C)(2) for volume marking
- Lightweight, durable TAYMAC TUFF® die-cast aluminium construction
- Tri-combo head set screws
- Captive screws with attached O-ring for ease of use and a weatherproof seal
- Includes (1) body, (3) blank covers/panels, (1) T panel, (1) LL/LB/LR panel, (2) 1/2 in. reducer bushings, (1) closure plug and extra hardware
- Ideal for service trucks and reduces inventory
- Not suitable for use in hazardous location applications

General

Catalog Number	UCB075
Conduit Type	Universal
Fitting Type	Conduit Bodies
Material	Aluminum
Type	Universal Conduit Bodies
UPC	050169571231

Dimensions

Dimensions	3.568 in x 5.754 in x 2.06 in
Height	2.06 in

Length	3.568 in
Trade Size	3/4 in
Weight	1.12 lb
Width	5.754 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Pallet Quantity	1280
Standard Package	10

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Sell Sheets - Service Truck Solutions](#)
[Sell Sheets - U-Conduit 10-in-1 Universal Conduit Body](#)
[Specifications - UCB075](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TAYMAC®: U-CONDUIT®](#)



A Hubbell brand