



2-Gang Metal Wallplate, Standard, 2-Blank, Ivory Smooth

By TayMac
Catalog # [WI-BB](#)

2-Gang Metal Wallplate, Standard, 2-Blank, Ivory Smooth



Features

- Easily primed and painted to match or complement walls.
- Won't bow, crack or distort during installation.
- Premium North American powder coat.
- Includes screw(s) in matching finish.

General

Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Finish Type	Smooth
Material	Metal
Number of Gang(s)	2-Gang
Size	Standard
Style	Blank
UPC	092326180979

Dimensions

Dimensions	0.17 in x 4.58 in x 4.52 in
Height	4.52 in
Length	0.17 in
Weight	0.22 lb
Width	4.58 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	100
Minimum Pack Quantity	10
Pallet Quantity	4500

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Catalogs - Wallplates and HVAC E1-E26](#)
- [Literature - IN-USE COVERS CONDUIT BODIES WALLPLATES](#)
- [Sales Drawings - Standard Metal Wallplates](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)

