



## 2-Gang Metal Wallplate, Standard, 2-Duplex, Ivory Smooth

By TayMac  
Catalog # WI-DD

2-Gang Metal Wallplate, Standard, 2-Duplex, Ivory Smooth



### Features

- Easily primed and painted to match or complement walls.
- Won't bow, crack or distort during installation.
- Premium North American powder coat.
- Includes screw(s) in matching finish.

### General

Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Finish Type	Smooth
Material	Metal
Number of Gang(s)	2-Gang
Size	Standard
Style	2-Duplex
UPC	092326180900

### Dimensions

Dimensions	0.17 in x 4.58 in x 4.52 in
Height	4.52 in
Length	0.17 in
Weight	0.161 lb
Width	4.58 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	100
Minimum Pack Quantity	10
Pallet Quantity	4500

### Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Catalogs - Wallplates and HVAC E1-E26](#)
- [Literature - IN-USE COVERS CONDUIT BODIES WALLPLATES](#)
- [Sales Drawings - Standard Metal Wallplates](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand