



# 2-Gang Metal Wallplate, Standard, 2-Toggle, Ivory Smooth

By TayMac  
Catalog # [WI-TT](#)



2-Gang Metal Wallplate, Standard, 2-Toggle, Ivory Smooth

## Features

- Easily primed and painted to match or complement walls.
- Won't bow, crack or distort during installation.
- Premium North American powder coat.
- Includes screw(s) in matching finish.

## General

Catalog Number	WI-TT
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Finish Type	Smooth
Material	Metal
Number of Gang(s)	2-Gang
Size	Standard
Style	2-Toggle
UPC	092326180870

## Dimensions

Dimensions	0.17 in x 4.563 in x 4.5 in
Height	4.5 in
Length	0.17 in

Weight	0.256 lb
Width	4.563 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed

## Logistics

Carton Quantity	100
Minimum Pack Quantity	10
Pallet Quantity	4500

## Product Assets

[Catalogs - Wallplates and HVAC E1-E26](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)  
[Literature - IN-USE COVERS CONDUIT BODIES WALLPLATES](#)  
[Sales Drawings - Standard Metal Wallplates](#)  
[SDS - HCC SDS](#)  
[Specifications - WITT](#)  
[Terms and Conditions - HCC Terms & Conditions](#)