



## 2-Gang Metal Wallplate, Maxi, Single Receptacle 2.15 in., Ivory Smooth

By TayMac  
Catalog # [WRI2-2](#)

2-Gang Metal Wallplate, Maxi, Single Receptacle 2.15 in., Ivory Smooth



### Features

- Easily primed and painted to match or complement walls.
- Won't bow, crack or distort during installation.
- Premium North American powder coat.
- Includes screw(s) in matching finish.

### General

Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Finish Type	Smooth
Material	Metal
Number of Gang(s)	2-Gang
Size	Maxi/Princess
Style	Single Outlet 2.15 in
UPC	092326116237

### Dimensions

Dimensions	0.12 in x 4.57 in x 5.01 in
Height	5.01 in
Length	0.12 in
Weight	0.282 lb
Width	4.57 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	100
Minimum Pack Quantity	10
Pallet Quantity	4500

### Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Catalogs - Wallplates and HVAC E1-E26](#)
- [Literature - IN-USE COVERS CONDUIT BODIES WALLPLATES](#)
- [Sales Drawings - Maxi Metal Wallplates](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand