



2-Gang Metal Wallplate, Standard, Single Receptacle 2.15 in. dia., Stainless Steel

By TayMac
Catalog # [WSS2-2](#)

2-Gang Metal Wallplate, Standard, Single Receptacle 2.15 in. dia., Stainless Steel



Features

- Easily primed and painted to match or complement walls.
- Won't bow, crack or distort during installation.
- Premium North American powder coat.
- Includes screw(s) in matching finish.

General

Color	Stainless Steel
EU RoHS Indicator	Contact Manufacturer
Material	Metal
Number of Gang(s)	2-Gang
Size	Standard
Style	Receptacle 2.25 in Hole
UPC	092326180191

Dimensions

Dimensions	0.17 in x 4.51 in x 4.51 in
Height	4.51 in
Length	0.17 in
Weight	0.159 lb
Width	4.51 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	150
Minimum Pack Quantity	10
Pallet Quantity	3750

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Catalogs - Wallplates and HVAC E1-E26](#)
- [Certifications - UL COC-E212332-2](#)
- [Literature - IN-USE COVERS CONDUIT BODIES WALLPLATES](#)
- [Sales Drawings - Standard Metal Wallplates](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand