



1-Gang Metal Wallplate, Standard, Single Receptacle 1.40 in., Stainless Steel

By TayMac
Catalog # [WSS-SR2](#)

1-Gang Metal Wallplate, Standard, Single Receptacle 1.40 in., Stainless Steel



Features

- Easily primed and painted to match or complement walls.
- Won't bow, crack or distort during installation.
- Premium North American powder coat.
- Includes screw(s) in matching finish.

General

Color	Stainless Steel
EU RoHS Indicator	Contact Manufacturer
Material	Metal
Number of Gang(s)	1-Gang
Size	Standard
Style	Receptacle 1.4 in Hole
UPC	092326180214

Dimensions

Dimensions	0.08 in x 2.76 in x 4.5 in
Height	4.5 in
Length	0.08 in
Weight	0.216 lb
Width	2.76 in

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity	250
Minimum Pack Quantity	10
Pallet Quantity	6250

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Catalogs - Wallplates and HVAC E1-E26](#)
[Certifications - UL COC-E212332-2](#)
[Literature - Metal Wall Plate Reference](#)
[Sales Drawings - Standard Metal Wallplates](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
TAYM-WSSSR2-SPEC-EN | REV 6/2024