



## 2-Gang Metal Wallplate, Standard, Toggle/Decorator, Stainless Steel

By TayMac  
Catalog # [WSS-TR](#)

2-Gang Metal Wallplate, Standard, Toggle/Decorator, Stainless Steel



### Features

- Easily primed and painted to match or complement walls.
- Won't bow, crack or distort during installation.
- Premium North American powder coat.
- Includes screw(s) in matching finish.

### General

Color	Stainless Steel
EU RoHS Indicator	Contact Manufacturer
Material	Metal
Number of Gang(s)	2-Gang
Size	Standard
Style	Toggle Decorator/Rocker
UPC	092326180030

### Dimensions

Dimensions	0.17 in x 4.58 in x 4.52 in
Height	4.52 in
Length	0.17 in
Weight	0.108 lb
Width	4.58 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	150
Minimum Pack Quantity	10
Pallet Quantity	3750

### Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Catalogs - Wallplates and HVAC E1-E26](#)
- [Certifications - UL COC-E212332-2](#)
- [Literature - IN-USE COVERS CONDUIT BODIES WALLPLATES](#)
- [Sales Drawings - Standard Metal Wallplates](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand