



## 2-Gang Metal Wallplate, Standard, 2-Toggle, Ivory Textured

By TayMac  
Catalog # [WTI-TT](#)

2-Gang Metal Wallplate, Standard, 2-Toggle, Ivory Textured



### Features

- Easily primed and painted to match or complement walls.
- Won't bow, crack or distort during installation.
- Premium North American powder coat.
- Includes screw(s) in matching finish.

### General

Color	Ivory
EU RoHS Indicator	Yes
Finish Type	Textured
Material	Metal
Number of Gang(s)	2-Gang
Size	Standard
Style	2-Toggle
UPC	092326117111

### Dimensions

Dimensions	0.17 in x 4.56 in x 4.51 in
Height	4.51 in
Length	0.17 in
Weight	0.194 lb
Width	4.56 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	100
Minimum Pack Quantity	10
Pallet Quantity	4500

### Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Catalogs - Wallplates and HVAC E1-E26](#)
- [Literature - IN-USE COVERS CONDUIT BODIES WALLPLATES](#)
- [Sales Drawings - Standard Metal Wallplates](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand