



4-Gang Metal Wallplate, Standard, 4-Toggle, White Smooth

By TayMac
Catalog # [WW-TTTT](#)



4-Gang Metal Wallplate, Standard, 4-Toggle, White Smooth

Features

- Easily primed and painted to match or complement walls.
- Won't bow, crack or distort during installation.
- Premium North American powder coat.
- Includes screw(s) in matching finish.

General

Color	White
EU RoHS Indicator	Contact Manufacturer
Finish Type	Smooth
Material	Metal
Number of Gang(s)	4-Gang
Size	Standard
Style	4-Toggle
UPC	092326116985

Dimensions

Dimensions	0.17 in x 8.19 in x 4.51 in
Height	4.51 in
Length	0.17 in
Weight	0.353 lb
Width	8.19 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Minimum Pack Quantity	10
Pallet Quantity	1250

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Catalogs - Wallplates and HVAC E1-E26](#)
- [Literature - IN-USE COVERS CONDUIT BODIES WALLPLATES](#)
- [Sales Drawings - Standard Metal Wallplates](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand