



# 2-Gang Weatherproof In-Use Cover, EXTRA DUTY®, 55-in-1, 2-3/4 in. Deep, Clear

By TayMac  
Catalog # [MM2420C](#)



2-Gang Weatherproof In-Use Cover, EXTRA DUTY®, 55-in-1, 2-3/4 in. Deep, Clear

### Features

- High-impact polycarbonate construction provides maximum durability
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast) for 55-in-1 custom device configurations, comes pre-configured for GFCI
- Lockable tab (1/8 in. shackle)
- Extra Duty® Rated
- Includes attached gasket and mounting hardware
- 2.75 in. deep
- Vertical mount

### Application

In Use

### General

Catalog Number	MM2420C
Color	Clear
Construction	Nonmetallic
Cover Type	In-Use
Material	Polycarbonate
Mounting Method	Vertical
Number of Gang(s)	2-Gang
Type	Cover
UPC	050169917305

### Dimensions

Actual Depth	3.07 in
--------------	---------

Cubic Capacity	82.12875 cu.in
Depth	2.75 in
Height	5.5 in
Weight	0.7 lb
Width	5.43 in

### Certifications And Compliance

Certified Listed	UL Listed
Compliance	Extra-Duty
NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	6
Packaging Type	Shrink
Pallet Quantity	576
Standard Package	6

### Product Assets

[360 Product View - TAYM\\_MM2420C](#)  
[3D Product View - MM2420C](#)  
[Certifications - UL COC-E116141-4](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Product Logo - ExtraDuty](#)  
[Sales Drawings - MM2420](#)  
[SDS - HCC SDS](#)  
[Specifications - MM2420C](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - TAYMAC®: Extra-Duty Overview](#)



A Hubbell brand